

JAVALTYICS™

Degree of Roast Analyzer Product Selection Guide

Feature/Model	JAV-RDA-H	JAV-RDA-U	JAV-RDA-DN	JAV-RDA-D
Portable	Yes	No	No	No
Glassware Required?	No	Yes	No	No
Number of Scales	1	4	4	4
Default Scales	Gourmet (~SCAA Tiles)	Gourmet (~SCAA Tiles) ² Commercial ² PB ² NEO ²	Gourmet (~SCAA Tiles) ² Commercial ² PB ² NEO ²	Gourmet (~SCAA Tiles) ² Commercial ² PB ² NEO ²
RoastMatch™ ¹	No	Yes	Yes	Yes
JAV-Net (web enabled)	Not Available	Optional	Optional	Included
Battery Operated	Yes	No	No	No
User Interface	Joystick and Buttons	Touchscreen	Touchscreen	Touchscreen
Portable	Yes	No	No	No
Power Supply Input	100-240VAC, 50-60Hz ³	100-240VAC, 50-60Hz	100-240VAC, 50-60Hz	100-240VAC, 50-60Hz
Travel Case	Optional	No	No	No
Comments	Portable Handheld	Lab Factory Competitive Research	Lab Factory Competitive Research	Lab Factory Competitive Research

1 - The RoastMatch™ Wizard makes matching and storage of scales easy.

This feature makes collaboration with different locations and different analyzers simple, regardless of the brand or location.

2 - Fully customizable using RoastMatch™ (JAV-RDA-U, JAV-RDA-DN, and JAV-RDA-D, only). See note 1, above.

3 - Only the charging cradle unit attaches to the power supply. The analyzer is handheld and operated exclusively using battery power.